

100lb Magnetic Mounting Hook System for WAL-RSL Series Rope Lights Hanging Hand Lamps and Drop Lights

3 inch diameter magnetic base with 100 pounds of magnetic grip. The MMSH-3-RSL includes a swivel hook for rope lights and cords. This allows operators to temporary mount rope lights from the ceiling, wall, or any metallic flat surface.

IMPORTANT

READ CAREFULLY BEFORE OPERATING. IF UNSURE ABOUT ANY PART OF THESE INSTRUCTIONS, CONSULT A QUALIFIED ELECTRICAL PROFESSIONAL.

WARNING: DO NOT ALLOW LINE VOLTAGE WIRES TO BECOME SUBMERGED WHEN EQUIPMENT ATTACHED!

- PEOPLE WITH PACEMAKERS SHOULD CONSULT THEIR PHYSICIAN(S) BEFORE USE. ELECTROMAGNETIC FIELDS IN CLOSE PROXIMITY TO HEART PACEMAKER COULD CAUSE PACEMAKER INTERFERENCE OR PACEMAKER FAILURE.
 - KEEP FINGERS AWAY FROM MAGNET WHEN MOUNTING AS INJURY COULD OCCUR.
-

Follow the basic steps below.

1. Attach magnetic mounting base to sturdy metal surface capable of holding the weight of attached equipment. The magnet can be mounted in any orientation.
2. Attach equipment to the swivel hook. This mounting base is suitable for hanging rope lights, hand lamps and drop lights. It can also be used for hanging line cord. **Note:** *When corded devices are attached, appropriately mark the area to prevent cord snags which could potentially cause the magnet and attached device to dismount.*
3. When removing magnet, do not slide as this could scratch the surface. Instead, pull the magnet directly off the surface.



THESE INSTRUCTIONS MAY NOT COVER ALL DETAILS OR VARIATIONS OF THIS PRODUCT FOR YOUR EQUIPMENT OR INSTALLATION REQUIREMENTS. SHOULD FURTHER INFORMATION NOT COVERED BY THESE INSTRUCTIONS BE REQUIRED, PLEASE CONTACT LARSON ELECTRONICS BY EMAIL AT SALES@LARSONELECTRONICS.COM OR BY PHONE AT 1-800-369-6671 FOR FURTHER ASSISTANCE.

PLEASE VISIT LARSONELECTRONICS.COM FOR **WARRANTY** AND **RETURN** INFORMATION.